ROYAL CHROME - 9 (E 8018 B8)

AWS: SFA 5.5, E 8018 B8 EN ISO 3580 A E CrMo 9 B 32 H5

Applications

It is used for welding of 9% Cr, plates, pipes, tubes It is also used for welding of 7 to 10% Cr, 1% Mo steels, for general corrosion and heat resistance application, Surfacing of turbine Blades, Valve, Seats, Pump parts etc.,

Characteristics on Usage

A heavy coated low hydrogen electrode specially developed for welding of Ferritic, Martensitic chrome steels. It gives weld deposit which has contain 9% Cr, 1% Mo having excellent creep strength upto 625 oC and resistance to oxidising atmosphere upto 700 oC. Proper preheating and post heating is required for welds made with these electrodes. The weld deposit gives radiographic quality of welds. Dry the electrode at 300 oC before welding to obtain best results.

Notes On Usage

- \checkmark Preheat at 150-250 °C and postheat at 740 ± 15 °C.
- Try the electrode at 250 300 °C for 60 Min-before use.

Welding Positions



Approvals

K.N.P.C.

Packing

Vaccum Pack

Chemical Composition Of Weld Metal

C%	Mn%	Si%	\$%	P%	Cr %	Ni %	Mo %	
0.05 - 0.10	1.0 Max	0.90 Max	0.030 Max	0.030 Max	8.0-10.5	0.40 Max	0.85 – 1.20	

Mechanical Properties Of Weld Metal

U.T.S.	Y.S.	ELONGATION	
(N/mm²)	(N/mm²)	(L = 4d) %	
550 Min	460 Min	19 % Min	

Packing and Welding Current

SIZE (mm)	KG PER PACKET	KG PER CARTON	LBS PER PACKET	LBS PER CARTON	In Amps	Current (Amps)
2.50 x 350	2	10	11	44	60-90	DC (+)
3.15 x 350/450	2	10	11	44	100 – 140	
4.00 x 350/450	2	10	11	44	140 – 180	
5.00 x 350/450	2	10	11	44	180 – 230	

